






















 375 nm	 450/45 BP	NUV450	BUV395, DAPI
	 525/40 BP	NUV525	BUV496
	 675/30 BP	NUV675	Hoescht Red, BUV661
 405 nm	 450/45 BP	V450-PB	Pacific Blue™ dye, V450, eFluor™ 450, BV421
	 525/40 BP	V525-KrO	Krome Orange, AmCyan, V500, BV510
	 610/20 BP	V610	BV605, Qdot® 605
	 660/10 BP	V660	BV650, Qdot® 655
	 763/43 BP	V763	BV785, Qdot® 800
 488 nm	 525/40 BP	B525-FITC	FITC, Alexa Fluor™ 488, CFSE, Fluor-3
	 610/20 BP	B610-ECD	ECD, PE-Texas Red®, PE-CF594, PI
	 690/50 BP	B690-PC5.5	PC5.5, PC5, PerCP, PerCP-Cy5.5, PI, DRAQ7™
 561 nm	 610/20 BP	Y610-mCherry	mCherry, ECD, PE-CF594
	 763/43 BP	Y763-PC7	PC7
	 585/42 BP	Y585-PE	PE, DsRed
	 675/30 BP	Y675-PC5	PC5, mPlum
	 710/50 BP	Y710-PC5.5	PC5.5, PE-AF680 <i>perCP</i>
 638 nm	 763/43 BP	R763-APCA750	APC-A750, APC-Cy7, APC-H7, APC- eFluor™ 780, DRAQ7™
	 660/10 BP	R660-APC	APC, Alexa Fluor™ 647, eFluor™ 660, Cy5
	 712/25 BP	R712-APCA700	APC-A700, Alexa Fluor™ 700, Cy5.5